

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202570

Luminaire Tested: **LE_6B60D010R EC6B60708050 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202570
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708050 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8121.7 lumens
Efficiency: N/A
Efficacy: 129.9 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202570

CATALOG NUMBER: LE_6B60D010R EC6B60708050 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202570

CATALOG NUMBER: LE_6B60D010R EC6B60708050 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47			
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42			
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38			
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35			
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202570

CATALOG NUMBER: LE_6B60D010R EC6B60708050 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	434.5	5.3
10°-20°	1135.9	14.0
20°-30°	1506.1	18.5
30°-40°	1606.5	19.8
40°-50°	1501.7	18.5
50°-60°	1145.1	14.1
60°-70°	622.9	7.7
70°-80°	167.0	2.1
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3076.5	37.9
0°-40°	4683.0	57.7
0°-60°	7329.8	90.2
0°-90°	8121.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8121.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4696	
5°	4632	435
15°	4050	1136
25°	3279	1506
35°	2567	1606
45°	1955	1502
55°	1288	1145
65°	622	623
75°	144	167
85°	0	2
90°	0	



TEST NUMBER: P202570

CATALOG NUMBER: LE_6B60D010R EC6B60708050 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4696.5
2.5°	4681.5
5°	4631.8
7.5°	4527.2
10°	4407.9
12.5°	4238.8
15°	4049.8
17.5°	3860.6
20°	3656.6
22.5°	3462.6
25°	3278.6
27.5°	3084.5
30°	2900.5
32.5°	2721.4
35°	2567.1
37.5°	2412.9
40°	2253.8
42.5°	2109.4
45°	1955.2
47.5°	1786.0
50°	1626.9
52.5°	1457.8
55°	1288.5
57.5°	1104.5
60°	935.4
62.5°	776.1
65°	621.9
67.5°	482.6
70°	353.2
72.5°	243.8
75°	144.2
77.5°	64.6
80°	14.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)