

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205049

Luminaire Tested: **LE_6B60D010R EC6B60709050 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205049
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709050 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6691.3 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205049

CATALOG NUMBER: LE_6B60D010R EC6B60709050 6LBSC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P205049

CATALOG NUMBER: LE_6B60D010R EC6B60709050 6LBSC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205049

CATALOG NUMBER: LE_6B60D010R EC6B60709050 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.6	4.3
10°-20°	812.5	12.1
20°-30°	1186.8	17.7
30°-40°	1357.4	20.3
40°-50°	1304.6	19.5
50°-60°	1007.4	15.1
60°-70°	562.3	8.4
70°-80°	163.7	2.4
80°-90°	7.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2288.9	34.2
0°-40°	3646.3	54.5
0°-60°	5958.3	89.0
0°-90°	6691.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6691.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3073	
5°	3047	290
15°	2882	813
25°	2579	1187
35°	2173	1357
45°	1701	1305
55°	1130	1007
65°	563	562
75°	143	164
85°	4	7
90°	0	



TEST NUMBER: P205049

CATALOG NUMBER: LE_6B60D010R EC6B60709050 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3072.8
2.5°	3072.8
5°	3046.8
7.5°	3033.8
10°	2990.5
12.5°	2938.6
15°	2882.4
17.5°	2826.1
20°	2743.9
22.5°	2678.9
25°	2579.4
27.5°	2479.9
30°	2380.2
32.5°	2280.8
35°	2172.6
37.5°	2064.4
40°	1938.9
42.5°	1826.4
45°	1700.9
47.5°	1558.0
50°	1423.9
52.5°	1276.8
55°	1129.5
57.5°	978.1
60°	835.2
62.5°	692.5
65°	562.6
67.5°	441.5
70°	328.9
72.5°	229.4
75°	142.9
77.5°	73.6
80°	26.0
82.5°	8.6
85°	4.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)