

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205558

Luminaire Tested: **LE\_6B60D010R EC6B60709050 6LBMGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205558  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60709050 6LBMGPH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3629.9 lumens  
Efficiency: N/A  
Efficacy: 58.1 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205558

CATALOG NUMBER: LE\_6B60D010R EC6B60709050 6LBMGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205558

CATALOG NUMBER: LE\_6B60D010R EC6B60709050 6LBMGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205558

CATALOG NUMBER: LE\_6B60D010R EC6B60709050 6LBMGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	347.5	9.6
10°-20°	901.7	24.8
20°-30°	1148.8	31.6
30°-40°	811.9	22.4
40°-50°	296.4	8.2
50°-60°	82.2	2.3
60°-70°	29.8	0.8
70°-80°	10.6	0.3
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2398.0	66.1
0°-40°	3209.9	88.4
0°-60°	3588.5	98.9
0°-90°	3629.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3629.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3783	
5°	3717	347
15°	3211	902
25°	2551	1149
35°	1290	812
45°	359	296
55°	88	82
65°	29	30
75°	7	11
85°	0	1
90°	0	



TEST NUMBER: P205558

CATALOG NUMBER: LE\_6B60D010R EC6B60709050 6LBMGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3782.6
2.5°	3767.9
5°	3716.6
7.5°	3614.0
10°	3504.0
12.5°	3357.4
15°	3210.8
17.5°	3064.1
20°	2917.5
22.5°	2741.6
25°	2551.0
27.5°	2287.1
30°	1993.9
32.5°	1642.0
35°	1290.1
37.5°	982.2
40°	718.4
42.5°	520.5
45°	359.2
47.5°	241.9
50°	161.2
52.5°	110.0
55°	88.0
57.5°	66.0
60°	51.4
62.5°	36.6
65°	29.4
67.5°	22.0
70°	14.6
72.5°	14.6
75°	7.4
77.5°	7.4
80°	7.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)