

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203297

Luminaire Tested: **LE\_6B60D010R EC6B60709050 6LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203297  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60709050 6LBMH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4755.5 lumens  
Efficiency: N/A  
Efficacy: 76.1 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203297

CATALOG NUMBER: LE\_6B60D010R EC6B60709050 6LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203297

CATALOG NUMBER: LE\_6B60D010R EC6B60709050 6LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203297

CATALOG NUMBER: LE\_6B60D010R EC6B60709050 6LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	430.3	9.0
10°-20°	1113.2	23.4
20°-30°	1442.4	30.3
30°-40°	1070.9	22.5
40°-50°	452.1	9.5
50°-60°	160.5	3.4
60°-70°	62.0	1.3
70°-80°	21.5	0.5
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2985.8	62.8
0°-40°	4056.7	85.3
0°-60°	4669.3	98.2
0°-90°	4755.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4755.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4706	
5°	4604	430
15°	3973	1113
25°	3198	1442
35°	1698	1071
45°	557	452
55°	170	161
65°	61	62
75°	20	21
85°	0	3
90°	0	



TEST NUMBER: P203297

CATALOG NUMBER: LE\_6B60D010R EC6B60709050 6LBMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4706.0
2.5°	4692.5
5°	4604.1
7.5°	4475.1
10°	4319.0
12.5°	4149.2
15°	3972.6
17.5°	3775.8
20°	3599.1
22.5°	3415.8
25°	3198.5
27.5°	2899.6
30°	2546.6
32.5°	2132.4
35°	1697.8
37.5°	1331.0
40°	1011.9
42.5°	753.8
45°	556.9
47.5°	407.5
50°	298.8
52.5°	224.1
55°	169.8
57.5°	129.0
60°	101.9
62.5°	74.8
65°	61.1
67.5°	47.5
70°	34.0
72.5°	27.1
75°	20.4
77.5°	13.6
80°	6.8
82.5°	6.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)