

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205251

Luminaire Tested: **LE_6B60D010R EC6B60709050 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205251
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709050 6LBWL1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6574.2 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205251

CATALOG NUMBER: LE_6B60D010R EC6B60709050 6LBWL11

Luminous Intensity Polar Plot





TEST NUMBER: P205251

CATALOG NUMBER: LE_6B60D010R EC6B60709050 6LBWL11

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69			69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205251

CATALOG NUMBER: LE_6B60D010R EC6B60709050 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	396.2	6.0
10°-20°	1190.9	18.1
20°-30°	1795.2	27.3
30°-40°	1837.4	27.9
40°-50°	1070.4	16.3
50°-60°	246.0	3.7
60°-70°	30.2	0.5
70°-80°	7.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3382.2	51.4
0°-40°	5219.7	79.4
0°-60°	6536.0	99.4
0°-90°	6574.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6574.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4107	
5°	4129	396
15°	4219	1191
25°	3936	1795
35°	2982	1837
45°	1379	1070
55°	238	246
65°	22	30
75°	8	8
85°	0	0
90°	0	



TEST NUMBER: P205251

CATALOG NUMBER: LE_6B60D010R EC6B60709050 6LBWL11

CANDELA DISTRIBUTION (FULL):

	0°
0°	4107.0
2.5°	4099.5
5°	4129.4
7.5°	4159.1
10°	4196.4
12.5°	4203.9
15°	4218.8
17.5°	4203.9
20°	4166.6
22.5°	4047.4
25°	3935.5
27.5°	3756.6
30°	3525.6
32.5°	3287.0
35°	2981.5
37.5°	2638.6
40°	2258.5
42.5°	1833.6
45°	1378.9
47.5°	961.5
50°	633.5
52.5°	402.5
55°	238.5
57.5°	126.8
60°	67.1
62.5°	37.2
65°	22.4
67.5°	22.4
70°	14.9
72.5°	7.5
75°	7.5
77.5°	7.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)