

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844319

Luminaire Tested: **LD6C30DE010B40 EU6C30B40 6LBCSMMS**

Issue Date: 5/7/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P844319  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204757)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C30DE010B40 EU6C30B40 6LBCSMMS  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2922.2 lumens  
Efficiency: N/A  
Efficacy: 85.7 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 34.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844319

CATALOG NUMBER: LD6C30DE010B40 EU6C30B40 6LBCSMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P844319

CATALOG NUMBER: LD6C30DE010B40 EU6C30B40 6LBCSMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	65433
5°	65381
10°	65357
15°	64734
20°	64260
25°	63621
30°	62541
35°	61516
40°	59698
45°	57673
50°	54224
55°	49088
60°	43089
65°	36281
70°	28402
75°	19889
80°	11144
85°	7737



TEST NUMBER: P844319

CATALOG NUMBER: LD6C30DE010B40 EU6C30B40 6LBCSMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.1	3.9
10°-20°	322.0	11.0
20°-30°	484.3	16.6
30°-40°	574.0	19.6
40°-50°	571.2	19.5
50°-60°	460.5	15.8
60°-70°	278.5	9.5
70°-80°	103.4	3.5
80°-90°	15.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	919.3	31.5
0°-40°	1493.3	51.1
0°-60°	2524.9	86.4
0°-90°	2922.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2922.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1194	
5°	1188	113
15°	1141	322
25°	1052	484
35°	919	574
45°	744	571
55°	514	460
65°	280	278
75°	94	103
85°	12	15
90°	0	



TEST NUMBER: P844319

CATALOG NUMBER: LD6C30DE010B40 EU6C30B40 6LBCSMMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1193.6
2.5°	1193.6
5°	1188.1
7.5°	1184.8
10°	1174.1
12.5°	1156.2
15°	1140.6
17.5°	1122.8
20°	1101.5
22.5°	1080.2
25°	1051.8
27.5°	1021.8
30°	988.0
32.5°	956.3
35°	919.2
37.5°	880.2
40°	834.2
42.5°	789.6
45°	743.9
47.5°	692.3
50°	635.8
52.5°	577.3
55°	513.6
57.5°	456.9
60°	393.0
62.5°	336.5
65°	279.7
67.5°	226.5
70°	177.2
72.5°	132.9
75°	93.9
77.5°	60.2
80°	35.3
82.5°	21.2
85°	12.3
87.5°	5.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)