

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844328

Luminaire Tested: **LD6C30DE010B40 EU6C30B40 6LBMMW**

Issue Date: 5/7/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P844328  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C30DE010B40 EU6C30B40 6LBMMW  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2278.1 lumens  
Efficiency: N/A  
Efficacy: 66.8 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 34.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844328

CATALOG NUMBER: LD6C30DE010B40 EU6C30B40 6LBMMW

### Luminous Intensity Polar Plot





TEST NUMBER: P844328

CATALOG NUMBER: LD6C30DE010B40 EU6C30B40 6LBMMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	93183
5°	91987
10°	88854
15°	85063
20°	80840
25°	75264
30°	64839
35°	49209
40°	35975
45°	27282
50°	22242
55°	19517
60°	17915
65°	16318
70°	14602
75°	13302
80°	11933
85°	9875



TEST NUMBER: P844328

CATALOG NUMBER: LD6C30DE010B40 EU6C30B40 6LBMWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.0	6.9
10°-20°	420.6	18.5
20°-30°	564.8	24.8
30°-40°	463.3	20.3
40°-50°	278.2	12.2
50°-60°	184.9	8.1
60°-70°	123.9	5.4
70°-80°	66.7	2.9
80°-90°	18.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1142.4	50.1
0°-40°	1605.7	70.5
0°-60°	2068.7	90.8
0°-90°	2278.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2278.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1700	
5°	1672	157
15°	1499	421
25°	1244	565
35°	735	463
45°	352	278
55°	204	185
65°	126	124
75°	63	67
85°	16	19
90°	0	



TEST NUMBER: P844328

CATALOG NUMBER: LD6C30DE010B40 EU6C30B40 6LBMMW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1699.8
2.5°	1687.2
5°	1671.6
7.5°	1637.0
10°	1596.2
12.5°	1545.8
15°	1498.8
17.5°	1442.2
20°	1385.7
22.5°	1322.9
25°	1244.3
27.5°	1150.0
30°	1024.3
32.5°	882.9
35°	735.3
37.5°	609.5
40°	502.7
42.5°	417.9
45°	351.9
47.5°	298.5
50°	260.8
52.5°	229.4
55°	204.2
57.5°	182.2
60°	163.4
62.5°	141.4
65°	125.8
67.5°	106.8
70°	91.1
72.5°	75.4
75°	62.8
77.5°	50.2
80°	37.8
82.5°	28.2
85°	15.7
87.5°	6.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)