

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208955

Luminaire Tested: **LDSQA6A55940D010TE LARH30NF 6LSQA1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208955
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26623)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A55940D010TE LARH30NF 6LSQA1H
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4478.4 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.57 / 0.55
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 60.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208955

CATALOG NUMBER: LDSQA6A55940D010TE LARH30NF 6LSQA1H

Luminous Intensity Polar Plot





TEST NUMBER: P208955

CATALOG NUMBER: LDSQA6A55940D010TE LARH30NF 6LSQA1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	92			
3	107	102	98	95	105	101	97	95	98	95	93	96	94	92	94	92	90	89			
4	103	98	94	90	102	97	93	90	95	91	89	93	90	88	91	89	87	86			
5	100	94	89	86	99	93	89	86	91	88	85	90	87	84	88	86	84	83			
6	97	90	86	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80			
7	94	87	82	79	93	86	82	79	85	81	79	84	81	78	83	80	78	77			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72			
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	73	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	568748
5°	526801
10°	469306
15°	358116
20°	214698
25°	118325
30°	29273
35°	2260
40°	641
45°	250
50°	107
55°	120
60°	138
65°	82
70°	101
75°	133
80°	198
85°	0



TEST NUMBER: P208955

CATALOG NUMBER: LDSQA6A55940D010TE LARH30NF 6LSQA1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1121.4	25.0
10°-20°	2149.7	48.0
20°-30°	1110.2	24.8
30°-40°	90.0	2.0
40°-50°	3.7	0.1
50°-60°	1.4	0.0
60°-70°	1.1	0.0
70°-80°	0.8	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4381.3	97.8
0°-40°	4471.3	99.8
0°-60°	4476.4	100.0
0°-90°	4478.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4478.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13210	
5°	12189	###
15°	8034	2150
25°	2491	1110
35°	43	90
45°	4	4
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P208955

CATALOG NUMBER: LDSQA6A55940D010TE LARH30NF 6LSQA1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	13209.6
2.5°	12908.3
5°	12188.8
7.5°	11533.5
10°	10734.4
12.5°	9659.9
15°	8034.1
17.5°	6228.8
20°	4685.8
22.5°	3435.2
25°	2490.7
27.5°	1500.0
30°	588.8
32.5°	250.1
35°	43.0
37.5°	21.1
40°	11.4
42.5°	6.5
45°	4.1
47.5°	2.4
50°	1.6
52.5°	1.6
55°	1.6
57.5°	1.6
60°	1.6
62.5°	1.6
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)