

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844516

Luminaire Tested: **LD6C40DE010B50 EU6C40B50 6LBNH**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P844516  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C40DE010B50 EU6C40B50 6LBNH  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3363.3 lumens  
Efficiency: N/A  
Efficacy: 67.5 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 49.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844516

CATALOG NUMBER: LD6C40DE010B50 EU6C40B50 6LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P844516

CATALOG NUMBER: LD6C40DE010B50 EU6C40B50 6LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	236346
5°	230502
10°	212688
15°	188304
20°	163499
25°	139847
30°	115296
35°	75924
40°	40819
45°	18072
50°	7326
55°	5285
60°	3366
65°	2400
70°	1988
75°	1292
80°	1926
85°	0



TEST NUMBER: P844516

CATALOG NUMBER: LD6C40DE010B50 EU6C40B50 6LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	387.7	11.5
10°-20°	924.6	27.5
20°-30°	1059.2	31.5
30°-40°	711.7	21.2
40°-50°	203.3	6.0
50°-60°	49.8	1.5
60°-70°	18.9	0.6
70°-80°	7.3	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2371.5	70.5
0°-40°	3083.1	91.7
0°-60°	3336.2	99.2
0°-90°	3363.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3363.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4311	
5°	4189	388
15°	3318	925
25°	2312	1059
35°	1134	712
45°	233	203
55°	55	50
65°	18	19
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P844516

CATALOG NUMBER: LD6C40DE010B50 EU6C40B50 6LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4311.3
2.5°	4280.8
5°	4188.7
7.5°	4023.0
10°	3820.8
12.5°	3563.1
15°	3317.9
17.5°	3060.4
20°	2802.6
22.5°	2557.4
25°	2312.0
27.5°	2085.1
30°	1821.4
32.5°	1471.8
35°	1134.5
37.5°	827.9
40°	570.4
42.5°	374.1
45°	233.1
47.5°	141.0
50°	85.9
52.5°	67.4
55°	55.3
57.5°	42.9
60°	30.7
62.5°	24.4
65°	18.5
67.5°	12.4
70°	12.4
72.5°	6.1
75°	6.1
77.5°	6.1
80°	6.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)