

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843894

Luminaire Tested: **LD6C08DE010B40 EU6C08B40 6LBCSMMS**

Issue Date: 5/7/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P843894  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204757)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C08DE010B40 EU6C08B40 6LBCSMMS  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 858.7 lumens  
Efficiency: N/A  
Efficacy: 89.5 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843894

CATALOG NUMBER: LD6C08DE010B40 EU6C08B40 6LBCSMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P843894

CATALOG NUMBER: LD6C08DE010B40 EU6C08B40 6LBCSMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	19231
5°	19216
10°	19205
15°	19024
20°	18884
25°	18697
30°	18376
35°	18076
40°	17547
45°	16947
50°	15940
55°	14422
60°	12663
65°	10663
70°	8335
75°	5846
80°	3283
85°	2264



TEST NUMBER: P843894

CATALOG NUMBER: LD6C08DE010B40 EU6C08B40 6LBCSMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	33.2	3.9
10°-20°	94.6	11.0
20°-30°	142.3	16.6
30°-40°	168.7	19.6
40°-50°	167.9	19.5
50°-60°	135.3	15.8
60°-70°	81.8	9.5
70°-80°	30.4	3.5
80°-90°	4.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.2	31.5
0°-40°	438.8	51.1
0°-60°	742.0	86.4
0°-90°	858.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	858.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	351	
5°	349	33
15°	335	95
25°	309	142
35°	270	169
45°	219	168
55°	151	135
65°	82	82
75°	28	30
85°	4	5
90°	0	



TEST NUMBER: P843894

CATALOG NUMBER: LD6C08DE010B40 EU6C08B40 6LBCSMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	350.8
2.5°	350.8
5°	349.2
7.5°	348.2
10°	345.0
12.5°	339.8
15°	335.2
17.5°	330.0
20°	323.7
22.5°	317.4
25°	309.1
27.5°	300.3
30°	290.3
32.5°	281.0
35°	270.1
37.5°	258.7
40°	245.2
42.5°	232.0
45°	218.6
47.5°	203.5
50°	186.9
52.5°	169.6
55°	150.9
57.5°	134.2
60°	115.5
62.5°	98.9
65°	82.2
67.5°	66.6
70°	52.0
72.5°	39.0
75°	27.6
77.5°	17.7
80°	10.4
82.5°	6.2
85°	3.6
87.5°	1.6
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)