

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843901

Luminaire Tested: **LD6C08DE010B40 EU6C08B40 6LBMH**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P843901  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C08DE010B40 EU6C08B40 6LBMH  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 610.2 lumens  
Efficiency: N/A  
Efficacy: 63.6 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843901

CATALOG NUMBER: LD6C08DE010B40 EU6C08B40 6LBMH

### Luminous Intensity Polar Plot





TEST NUMBER: P843901

CATALOG NUMBER: LD6C08DE010B40 EU6C08B40 6LBMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	33106
5°	32517
10°	30856
15°	28933
20°	26947
25°	24830
30°	20687
35°	14583
40°	9296
45°	5543
50°	3275
55°	2084
60°	1436
65°	1012
70°	689
75°	551
80°	253
85°	0



TEST NUMBER: P843901

CATALOG NUMBER: LD6C08DE010B40 EU6C08B40 6LBMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.2	9.0
10°-20°	142.8	23.4
20°-30°	185.1	30.3
30°-40°	137.4	22.5
40°-50°	58.0	9.5
50°-60°	20.6	3.4
60°-70°	7.9	1.3
70°-80°	2.8	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	383.2	62.8
0°-40°	520.6	85.3
0°-60°	599.2	98.2
0°-90°	610.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	610.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	604	
5°	591	55
15°	510	143
25°	410	185
35°	218	137
45°	72	58
55°	22	21
65°	8	8
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P843901

CATALOG NUMBER: LD6C08DE010B40 EU6C08B40 6LBMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	603.9
2.5°	602.2
5°	590.9
7.5°	574.3
10°	554.3
12.5°	532.4
15°	509.8
17.5°	484.5
20°	461.9
22.5°	438.4
25°	410.5
27.5°	372.1
30°	326.8
32.5°	273.6
35°	217.9
37.5°	170.8
40°	129.9
42.5°	96.8
45°	71.5
47.5°	52.2
50°	38.4
52.5°	28.8
55°	21.8
57.5°	16.5
60°	13.1
62.5°	9.6
65°	7.8
67.5°	6.1
70°	4.3
72.5°	3.5
75°	2.6
77.5°	1.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)