

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843922

Luminaire Tested: **LD6C08DE010B50 EU6C08B50 6LBNLI**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P843922  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C08DE010B50 EU6C08B50 6LBNLI  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 708.7 lumens  
Efficiency: N/A  
Efficacy: 73.8 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843922

CATALOG NUMBER: LD6C08DE010B50 EU6C08B50 6LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P843922

CATALOG NUMBER: LD6C08DE010B50 EU6C08B50 6LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	88441
5°	82709
10°	67456
15°	49643
20°	34215
25°	25399
30°	19079
35°	11899
40°	5775
45°	1985
50°	264
55°	191
60°	121
65°	143
70°	176
75°	0
80°	0
85°	0



TEST NUMBER: P843922

CATALOG NUMBER: LD6C08DE010B50 EU6C08B50 6LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.1	18.9
10°-20°	240.8	34.0
20°-30°	194.7	27.5
30°-40°	112.1	15.8
40°-50°	23.7	3.4
50°-60°	2.0	0.3
60°-70°	1.1	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	569.6	80.4
0°-40°	681.7	96.2
0°-60°	707.5	99.8
0°-90°	708.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	708.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1613	
5°	1503	134
15°	875	241
25°	420	195
35°	178	112
45°	26	24
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P843922

CATALOG NUMBER: LD6C08DE010B50 EU6C08B50 6LBNLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1613.3
2.5°	1594.0
5°	1503.0
7.5°	1372.3
10°	1211.8
12.5°	1047.3
15°	874.7
17.5°	708.1
20°	586.5
22.5°	493.5
25°	419.9
27.5°	357.6
30°	301.4
32.5°	239.1
35°	177.8
37.5°	123.6
40°	80.7
42.5°	49.1
45°	25.6
47.5°	10.3
50°	3.1
52.5°	3.1
55°	2.0
57.5°	2.0
60°	1.1
62.5°	1.1
65°	1.1
67.5°	1.1
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)