

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843926

Luminaire Tested: **LD6C08DE010B50 EU6C08B50 6LBWLI**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843926
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C08DE010B50 EU6C08B50 6LBWLI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 900.1 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843926

CATALOG NUMBER: LD6C08DE010B50 EU6C08B50 6LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P843926

CATALOG NUMBER: LD6C08DE010B50 EU6C08B50 6LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92			92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69			69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	45	44			44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30820
5°	31108
10°	31980
15°	32781
20°	33276
25°	32591
30°	30555
35°	27318
40°	22120
45°	14637
50°	7394
55°	3125
60°	1009
65°	402
70°	321
75°	233
80°	0
85°	0



TEST NUMBER: P843926

CATALOG NUMBER: LD6C08DE010B50 EU6C08B50 6LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	6.0
10°-20°	163.0	18.1
20°-30°	245.8	27.3
30°-40°	251.5	27.9
40°-50°	146.6	16.3
50°-60°	33.7	3.7
60°-70°	4.2	0.5
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	463.1	51.4
0°-40°	714.6	79.4
0°-60°	894.8	99.4
0°-90°	900.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	900.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	562	
5°	565	54
15°	578	163
25°	539	246
35°	408	252
45°	189	147
55°	33	34
65°	3	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P843926

CATALOG NUMBER: LD6C08DE010B50 EU6C08B50 6LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	562.2
2.5°	561.3
5°	565.3
7.5°	569.4
10°	574.5
12.5°	575.6
15°	577.6
17.5°	575.6
20°	570.4
22.5°	554.1
25°	538.8
27.5°	514.3
30°	482.7
32.5°	450.0
35°	408.2
37.5°	361.2
40°	309.1
42.5°	251.1
45°	188.8
47.5°	131.7
50°	86.7
52.5°	55.1
55°	32.7
57.5°	17.3
60°	9.2
62.5°	5.1
65°	3.1
67.5°	3.1
70°	2.0
72.5°	1.1
75°	1.1
77.5°	1.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)