

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244452

Luminaire Tested: **LSR8B10D010 EC8B10830 8LBS0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244452  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B10D010 EC8B10830 8LBS0H  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1188.1 lumens  
Efficiency: N/A  
Efficacy: 116.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244452

CATALOG NUMBER: LSR8B10D010 EC8B10830 8LBS0H

### Luminous Intensity Polar Plot





TEST NUMBER: P244452

CATALOG NUMBER: LSR8B10D010 EC8B10830 8LBS0H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69	76	72	68	74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56	65	59	55	63	58	55	53
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	21259
5°	21188
10°	21029
15°	20878
20°	20739
25°	20466
30°	19833
35°	18713
40°	17007
45°	13994
50°	9326
55°	4860
60°	2288
65°	1204
70°	604
75°	417
80°	320
85°	248



TEST NUMBER: P244452

CATALOG NUMBER: LSR8B10D010 EC8B10830 8LBS0H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.9	5.5
10°-20°	184.6	15.5
20°-30°	276.2	23.2
30°-40°	308.9	26.0
40°-50°	242.3	20.4
50°-60°	88.4	7.4
60°-70°	18.0	1.5
70°-80°	3.9	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	525.7	44.2
0°-40°	834.6	70.2
0°-60°	1165.3	98.1
0°-90°	1188.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1188.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	689	
5°	684	65
15°	654	185
25°	602	276
35°	497	309
45°	321	242
55°	90	88
65°	16	18
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P244452

CATALOG NUMBER: LSR8B10D010 EC8B10830 8LBS0H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	689.4
2.5°	688.4
5°	684.5
7.5°	678.9
10°	671.6
12.5°	663.2
15°	654.0
17.5°	643.9
20°	632.0
22.5°	618.0
25°	601.5
27.5°	581.2
30°	557.0
32.5°	528.6
35°	497.1
37.5°	461.7
40°	422.5
42.5°	375.9
45°	320.9
47.5°	258.9
50°	194.4
52.5°	136.3
55°	90.4
57.5°	57.8
60°	37.1
62.5°	24.5
65°	16.5
67.5°	10.5
70°	6.7
72.5°	4.6
75°	3.5
77.5°	2.5
80°	1.8
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)