

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246474

Luminaire Tested: **LSR8B10D010 EC8B10835 8LBS0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246474
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B10D010 EC8B10835 8LBS0B
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1043.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246474

CATALOG NUMBER: LSR8B10D010 EC8B10835 8LBS0B

Luminous Intensity Polar Plot





TEST NUMBER: P246474

CATALOG NUMBER: LSR8B10D010 EC8B10835 8LBS0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87	91	88	85	88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56	65	60	55	64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18631
5°	18610
10°	18515
15°	18379
20°	18176
25°	17890
30°	17365
35°	16548
40°	15325
45°	12860
50°	8501
55°	4199
60°	1665
65°	649
70°	99
75°	0
80°	0
85°	0



TEST NUMBER: P246474

CATALOG NUMBER: LSR8B10D010 EC8B10835 8LBS0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.1	5.5
10°-20°	162.3	15.6
20°-30°	241.6	23.2
30°-40°	273.6	26.2
40°-50°	221.2	21.2
50°-60°	76.7	7.4
60°-70°	10.5	1.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	460.9	44.2
0°-40°	734.5	70.4
0°-60°	1032.4	99.0
0°-90°	1043.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1043.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	604	
5°	601	57
15°	576	162
25°	526	242
35°	440	274
45°	295	221
55°	78	77
65°	9	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246474

CATALOG NUMBER: LSR8B10D010 EC8B10835 8LBS0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	604.2
2.5°	603.5
5°	601.2
7.5°	596.8
10°	591.3
12.5°	583.9
15°	575.7
17.5°	565.4
20°	553.9
22.5°	540.6
25°	525.8
27.5°	508.0
30°	487.7
32.5°	464.7
35°	439.6
37.5°	411.8
40°	380.7
42.5°	342.6
45°	294.9
47.5°	237.2
50°	177.2
52.5°	121.4
55°	78.1
57.5°	46.2
60°	27.0
62.5°	15.9
65°	8.9
67.5°	4.1
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)