

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208962

Luminaire Tested: **LDSQA6A65935D010TE LARH30NF 6LSQA1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26623)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A65935D010TE LARH30NF 6LSQA1H
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5162.8 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.57 / 0.55
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 78.67
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208962

CATALOG NUMBER: LDSQA6A65935D010TE LARH30NF 6LSQA1H

Luminous Intensity Polar Plot





TEST NUMBER: P208962

CATALOG NUMBER: LDSQA6A65935D010TE LARH30NF 6LSQA1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	92		
3	107	102	98	95	105	101	97	95	98	95	93	96	94	92	94	92	90	89		
4	103	98	94	90	102	97	93	90	95	91	89	93	90	88	91	89	87	86		
5	100	94	89	86	99	93	89	86	91	88	85	90	87	84	88	86	84	83		
6	97	90	86	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80		
7	94	87	82	79	93	86	82	79	85	81	79	84	81	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	73	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	655660
5°	607303
10°	541020
15°	412840
20°	247509
25°	136406
30°	33743
35°	2607
40°	736
45°	286
50°	127
55°	143
60°	164
65°	92
70°	113
75°	150
80°	223
85°	0



TEST NUMBER: P208962

CATALOG NUMBER: LDSQA6A65935D010TE LARH30NF 6LSQA1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1292.7	25.0
10°-20°	2478.3	48.0
20°-30°	1279.8	24.8
30°-40°	103.7	2.0
40°-50°	4.2	0.1
50°-60°	1.7	0.0
60°-70°	1.3	0.0
70°-80°	1.0	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5050.8	97.8
0°-40°	5154.5	99.8
0°-60°	5160.5	100.0
0°-90°	5162.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5162.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15228	
5°	14051	###
15°	9262	2478
25°	2871	1280
35°	50	104
45°	5	4
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P208962

CATALOG NUMBER: LDSQA6A65935D010TE LARH30NF 6LSQA1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	15228.2
2.5°	14880.9
5°	14051.4
7.5°	13295.9
10°	12374.7
12.5°	11136.1
15°	9261.8
17.5°	7180.6
20°	5401.9
22.5°	3960.1
25°	2871.3
27.5°	1729.2
30°	678.7
32.5°	288.3
35°	49.6
37.5°	24.3
40°	13.1
42.5°	7.5
45°	4.7
47.5°	2.8
50°	1.9
52.5°	1.9
55°	1.9
57.5°	1.9
60°	1.9
62.5°	1.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)