

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208994

Luminaire Tested: **LDSQA6A65935D010TE LARH40FL 6LSQA1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208994
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26677)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A65935D010TE LARH40FL 6LSQA1H
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5330.4 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.61
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 78.67
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208994

CATALOG NUMBER: LDSQA6A65935D010TE LARH40FL 6LSQA1H

Luminous Intensity Polar Plot





TEST NUMBER: P208994

CATALOG NUMBER: LDSQA6A65935D010TE LARH40FL 6LSQA1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	115	112	110	109	112	110	108	107		106	105	104			103	101	100			96
2	110	107	103	101	108	105	102	100		102	99	97			99	97	95			92
3	107	101	98	94	105	100	97	94		98	95	92			95	93	91			88
4	103	97	93	89	101	96	92	89		94	90	88			92	89	87			85
5	99	93	88	85	98	92	88	84		90	87	84			89	85	83			81
6	96	89	84	81	94	88	84	81		87	83	80			85	82	80			78
7	92	85	81	77	91	85	80	77		84	80	77			82	79	76			75
8	89	82	77	74	88	82	77	74		81	77	74			80	76	74			72
9	86	79	74	71	85	79	74	71		78	74	71			77	73	71			70
10	84	76	72	69	83	76	71	69		75	71	68			74	71	68			67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	593992
5°	517129
10°	467243
15°	426935
20°	312627
25°	154268
30°	34255
35°	6938
40°	1158
45°	341
50°	60
55°	68
60°	78
65°	92
70°	113
75°	0
80°	0
85°	0



TEST NUMBER: P208994

CATALOG NUMBER: LDSQA6A65935D010TE LARH40FL 6LSQA1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1109.1	20.8
10°-20°	2573.5	48.3
20°-30°	1509.6	28.3
30°-40°	130.6	2.5
40°-50°	5.7	0.1
50°-60°	0.8	0.0
60°-70°	0.9	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5192.2	97.4
0°-40°	5322.9	99.9
0°-60°	5329.3	100.0
0°-90°	5330.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5330.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13796	
5°	11965	###
15°	9578	2574
25°	3247	1510
35°	132	131
45°	6	6
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P208994

CATALOG NUMBER: LDSQA6A65935D010TE LARH40FL 6LSQA1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	13795.9
2.5°	12963.8
5°	11965.0
7.5°	11300.3
10°	10687.2
12.5°	10177.0
15°	9578.0
17.5°	8542.7
20°	6823.1
22.5°	4934.1
25°	3247.3
27.5°	1830.0
30°	689.0
32.5°	355.7
35°	132.0
37.5°	40.3
40°	20.6
42.5°	11.2
45°	5.6
47.5°	2.8
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)