

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246306

Luminaire Tested: **LSR8B10D010 EC8B10927 8LBW0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246306  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B10D010 EC8B10927 8LBW0B  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 2700 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 573.8 lumens  
Efficiency: N/A  
Efficacy: 56.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246306

CATALOG NUMBER: LSR8B10D010 EC8B10927 8LBW0B

### Luminous Intensity Polar Plot





TEST NUMBER: P246306

CATALOG NUMBER: LSR8B10D010 EC8B10927 8LBW0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71		78	74	70		76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56		65	60	56		64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49		57	52	49		57	52	49	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	16180
5°	15771
10°	15352
15°	15065
20°	14675
25°	14154
30°	12986
35°	9957
40°	4738
45°	1805
50°	878
55°	366
60°	93
65°	22
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246306

CATALOG NUMBER: LSR8B10D010 EC8B10927 8LBW0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.0	8.4
10°-20°	132.8	23.1
20°-30°	189.6	33.1
30°-40°	157.2	27.4
40°-50°	38.7	6.8
50°-60°	7.0	1.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.5	64.6
0°-40°	527.6	92.0
0°-60°	573.4	99.9
0°-90°	573.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	573.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	525	
5°	510	48
15°	472	133
25°	416	190
35°	264	157
45°	41	39
55°	7	7
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246306

CATALOG NUMBER: LSR8B10D010 EC8B10927 8LBW0B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	524.7
2.5°	520.3
5°	509.5
7.5°	499.0
10°	490.3
12.5°	481.8
15°	471.9
17.5°	460.2
20°	447.2
22.5°	432.3
25°	416.0
27.5°	393.9
30°	364.7
32.5°	323.7
35°	264.5
37.5°	191.1
40°	117.7
42.5°	68.5
45°	41.4
47.5°	27.3
50°	18.3
52.5°	11.9
55°	6.8
57.5°	3.2
60°	1.5
62.5°	0.6
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)