

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246288

Luminaire Tested: **LSR8B10D010 EC8B10935 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B10D010 EC8B10935 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 625.0 lumens
Efficiency: N/A
Efficacy: 61.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246288

CATALOG NUMBER: LSR8B10D010 EC8B10935 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P246288

CATALOG NUMBER: LSR8B10D010 EC8B10935 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71		78	74	70		76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56		65	60	56		64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49		57	52	49		57	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	17623
5°	17180
10°	16724
15°	16412
20°	15984
25°	15420
30°	14147
35°	10845
40°	5161
45°	1967
50°	959
55°	392
60°	99
65°	22
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246288

CATALOG NUMBER: LSR8B10D010 EC8B10935 8LBW0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	8.4
10°-20°	144.7	23.1
20°-30°	206.6	33.1
30°-40°	171.2	27.4
40°-50°	42.2	6.8
50°-60°	7.6	1.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	403.6	64.6
0°-40°	574.8	92.0
0°-60°	624.6	99.9
0°-90°	625.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	625.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	572	
5°	555	52
15°	514	145
25°	453	207
35°	288	171
45°	45	42
55°	7	8
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246288

CATALOG NUMBER: LSR8B10D010 EC8B10935 8LBW0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	571.5
2.5°	566.8
5°	555.0
7.5°	543.6
10°	534.1
12.5°	524.9
15°	514.1
17.5°	501.4
20°	487.1
22.5°	470.9
25°	453.2
27.5°	429.0
30°	397.3
32.5°	352.6
35°	288.1
37.5°	208.2
40°	128.2
42.5°	74.6
45°	45.1
47.5°	29.8
50°	20.0
52.5°	13.0
55°	7.3
57.5°	3.5
60°	1.6
62.5°	0.6
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)