

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245568

Luminaire Tested: **LSR8B10D010 EC8B10935 8LBW0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245568  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B10D010 EC8B10935 8LBW0GPH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 3500 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 867.0 lumens  
Efficiency: N/A  
Efficacy: 85.0 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245568

CATALOG NUMBER: LSR8B10D010 EC8B10935 8LBW0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245568

CATALOG NUMBER: LSR8B10D010 EC8B10935 8LBW0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	20818
5°	20324
10°	19689
15°	19403
20°	19174
25°	18764
30°	17575
35°	14350
40°	8566
45°	5146
50°	3708
55°	2521
60°	1585
65°	773
70°	198
75°	71
80°	53
85°	0



TEST NUMBER: P245568

CATALOG NUMBER: LSR8B10D010 EC8B10935 8LBW0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.8	7.1
10°-20°	171.5	19.8
20°-30°	251.9	29.1
30°-40°	228.3	26.3
40°-50°	97.7	11.3
50°-60°	43.2	5.0
60°-70°	11.5	1.3
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	485.2	56.0
0°-40°	713.5	82.3
0°-60°	854.5	98.6
0°-90°	867.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	867.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	675	
5°	657	62
15°	608	172
25°	552	252
35°	381	228
45°	118	98
55°	47	43
65°	11	12
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245568

CATALOG NUMBER: LSR8B10D010 EC8B10935 8LBW0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	675.1
2.5°	669.8
5°	656.6
7.5°	641.6
10°	628.8
12.5°	618.1
15°	607.8
17.5°	596.8
20°	584.3
22.5°	569.6
25°	551.5
27.5°	527.1
30°	493.6
32.5°	446.6
35°	381.2
37.5°	295.4
40°	212.8
42.5°	153.7
45°	118.0
47.5°	95.1
50°	77.3
52.5°	61.3
55°	46.9
57.5°	35.1
60°	25.7
62.5°	17.8
65°	10.6
67.5°	4.7
70°	2.2
72.5°	1.3
75°	0.6
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)