

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843946

Luminaire Tested: **LD6C10DE010B2750 EU6C10B30 6LBCSMW**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843946
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204757)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C10DE010B2750 EU6C10B30 6LBSCMW
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1282.9 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843946

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B30 6LBCSMW

Luminous Intensity Polar Plot





TEST NUMBER: P843946

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B30 6LBSCMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28731
5°	28703
10°	28690
15°	28417
20°	28218
25°	27933
30°	27454
35°	27010
40°	26213
45°	25320
50°	23803
55°	21552
60°	18913
65°	15929
70°	12454
75°	8727
80°	4893
85°	3397



TEST NUMBER: P843946

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B30 6LBCSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	3.9
10°-20°	141.4	11.0
20°-30°	212.6	16.6
30°-40°	252.0	19.6
40°-50°	250.8	19.5
50°-60°	202.1	15.8
60°-70°	122.3	9.5
70°-80°	45.4	3.5
80°-90°	6.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	403.6	31.5
0°-40°	655.6	51.1
0°-60°	1108.5	86.4
0°-90°	1282.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1282.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	524	
5°	522	50
15°	501	141
25°	462	213
35°	404	252
45°	327	251
55°	226	202
65°	123	122
75°	41	45
85°	5	7
90°	0	



TEST NUMBER: P843946

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B30 6LBCSMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	524.1
2.5°	524.1
5°	521.6
7.5°	520.1
10°	515.4
12.5°	507.7
15°	500.7
17.5°	493.0
20°	483.7
22.5°	474.1
25°	461.8
27.5°	448.5
30°	433.7
32.5°	419.9
35°	403.6
37.5°	386.5
40°	366.3
42.5°	346.7
45°	326.6
47.5°	304.0
50°	279.1
52.5°	253.4
55°	225.5
57.5°	200.5
60°	172.5
62.5°	147.8
65°	122.8
67.5°	99.5
70°	77.7
72.5°	58.4
75°	41.2
77.5°	26.4
80°	15.5
82.5°	9.3
85°	5.4
87.5°	2.3
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)