

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843952

Luminaire Tested: **LD6C10DE010B2750 EU6C10B30 6LBMH**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P843952
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C10DE010B2750 EU6C10B30 6LBMH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 854.6 lumens
Efficiency: N/A
Efficacy: 64.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843952

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B30 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P843952

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B30 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46361
5°	45531
10°	43208
15°	40517
20°	37727
25°	34768
30°	28966
35°	20418
40°	13010
45°	7760
50°	4580
55°	2915
60°	2006
65°	1427
70°	978
75°	784
80°	379
85°	0



TEST NUMBER: P843952

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B30 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.3	9.0
10°-20°	200.0	23.4
20°-30°	259.2	30.3
30°-40°	192.4	22.5
40°-50°	81.2	9.5
50°-60°	28.9	3.4
60°-70°	11.1	1.3
70°-80°	3.9	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.6	62.8
0°-40°	729.0	85.3
0°-60°	839.1	98.2
0°-90°	854.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	854.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	846	
5°	827	77
15°	714	200
25°	575	259
35°	305	192
45°	100	81
55°	30	29
65°	11	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P843952

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B30 6LBMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	845.7
2.5°	843.3
5°	827.4
7.5°	804.2
10°	776.2
12.5°	745.6
15°	713.9
17.5°	678.6
20°	646.7
22.5°	613.9
25°	574.8
27.5°	521.1
30°	457.6
32.5°	383.2
35°	305.1
37.5°	239.2
40°	181.8
42.5°	135.5
45°	100.1
47.5°	73.2
50°	53.7
52.5°	40.3
55°	30.5
57.5°	23.2
60°	18.3
62.5°	13.4
65°	11.0
67.5°	8.6
70°	6.1
72.5°	4.9
75°	3.7
77.5°	2.4
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)