

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244062

Luminaire Tested: **LSR8B10D010 EC8B10940 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B10D010 EC8B10940 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 4000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1135.0 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244062

CATALOG NUMBER: LSR8B10D010 EC8B10940 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P244062

CATALOG NUMBER: LSR8B10D010 EC8B10940 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88	91	88	86	88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63	71	66	62	69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19513
5°	19600
10°	19918
15°	20422
20°	20779
25°	20799
30°	20157
35°	18453
40°	16037
45°	12690
50°	8232
55°	4113
60°	1727
65°	759
70°	234
75°	119
80°	124
85°	106



TEST NUMBER: P244062

CATALOG NUMBER: LSR8B10D010 EC8B10940 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.5	5.3
10°-20°	180.8	15.9
20°-30°	280.0	24.7
30°-40°	304.1	26.8
40°-50°	221.0	19.5
50°-60°	75.1	6.6
60°-70°	12.0	1.1
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	521.3	45.9
0°-40°	825.4	72.7
0°-60°	1121.5	98.8
0°-90°	1135.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1135.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	633	
5°	633	61
15°	640	181
25°	611	280
35°	490	304
45°	291	221
55°	76	75
65°	10	12
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P244062

CATALOG NUMBER: LSR8B10D010 EC8B10940 8LBSOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	632.8
2.5°	632.8
5°	633.2
7.5°	634.1
10°	636.1
12.5°	638.4
15°	639.7
17.5°	638.4
20°	633.2
22.5°	623.7
25°	611.3
27.5°	592.8
30°	566.1
32.5°	530.6
35°	490.2
37.5°	446.3
40°	398.4
42.5°	346.7
45°	291.0
47.5°	231.1
50°	171.6
52.5°	117.5
55°	76.5
57.5°	46.6
60°	28.0
62.5°	17.3
65°	10.4
67.5°	5.9
70°	2.6
72.5°	1.6
75°	1.0
77.5°	0.7
80°	0.7
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)