

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244735

Luminaire Tested: **LSR8B15D010 EC8B15827 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15827 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 2700 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1292.0 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244735

CATALOG NUMBER: LSR8B15D010 EC8B15827 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244735

CATALOG NUMBER: LSR8B15D010 EC8B15827 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	59	65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58022
5°	57212
10°	52347
15°	44943
20°	37846
25°	31261
30°	23454
35°	13981
40°	6658
45°	2900
50°	1310
55°	575
60°	339
65°	190
70°	189
75°	0
80°	71
85°	318



TEST NUMBER: P244735

CATALOG NUMBER: LSR8B15D010 EC8B15827 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.7	13.2
10°-20°	392.3	30.4
20°-30°	416.2	32.2
30°-40°	237.5	18.4
40°-50°	58.9	4.6
50°-60°	11.6	0.9
60°-70°	3.5	0.3
70°-80°	0.8	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	979.2	75.8
0°-40°	1216.7	94.2
0°-60°	1287.1	99.6
0°-90°	1292.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1292.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1882	
5°	1848	171
15°	1408	392
25°	919	416
35°	371	237
45°	66	59
55°	11	12
65°	3	3
75°	0	1
85°	1	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P244735

CATALOG NUMBER: LSR8B15D010 EC8B15827 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1881.6
2.5°	1880.7
5°	1848.3
7.5°	1777.1
10°	1671.8
12.5°	1544.7
15°	1407.8
17.5°	1277.4
20°	1153.3
22.5°	1034.0
25°	918.8
27.5°	795.2
30°	658.7
32.5°	512.0
35°	371.4
37.5°	255.8
40°	165.4
42.5°	104.9
45°	66.5
47.5°	43.5
50°	27.3
52.5°	16.6
55°	10.7
57.5°	8.6
60°	5.5
62.5°	5.1
65°	2.6
67.5°	2.6
70°	2.1
72.5°	1.3
75°	0.0
77.5°	0.4
80°	0.4
82.5°	0.9
85°	0.9
87.5°	0.4
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P244735

CATALOG NUMBER: LSR8B15D010 EC8B15827 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)