

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843987

Luminaire Tested: **LD6C10DE010B2750 EU6C10B40 6LBMLI**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843987
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C10DE010B2750 EU6C10B40 6LBMLI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1063.9 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843987

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B40 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P843987

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B40 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72999
5°	72298
10°	68514
15°	62202
20°	54961
25°	47519
30°	37145
35°	22774
40°	11693
45°	4644
50°	1510
55°	516
60°	439
65°	350
70°	224
75°	297
80°	0
85°	0



TEST NUMBER: P843987

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B40 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	11.5
10°-20°	305.4	28.7
20°-30°	355.0	33.4
30°-40°	217.4	20.4
40°-50°	54.0	5.1
50°-60°	6.3	0.6
60°-70°	2.3	0.2
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	783.1	73.6
0°-40°	1000.4	94.0
0°-60°	1060.7	99.7
0°-90°	1063.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1063.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1332	
5°	1314	123
15°	1096	305
25°	786	355
35°	340	217
45°	60	54
55°	5	6
65°	3	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P843987

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B40 6LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1331.6
2.5°	1330.2
5°	1313.8
7.5°	1278.4
10°	1230.8
12.5°	1168.2
15°	1096.0
17.5°	1018.4
20°	942.1
22.5°	865.9
25°	785.6
27.5°	693.0
30°	586.8
32.5°	462.9
35°	340.3
37.5°	239.6
40°	163.4
42.5°	102.1
45°	59.9
47.5°	34.1
50°	17.7
52.5°	8.1
55°	5.4
57.5°	4.0
60°	4.0
62.5°	2.7
65°	2.7
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)