

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843990

Luminaire Tested: **LD6C10DE010B2750 EU6C10B40 6LBNLI**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P843990  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C10DE010B2750 EU6C10B40 6LBNLI  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 945.5 lumens  
Efficiency: N/A  
Efficacy: 71.1 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843990

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B40 6LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P843990

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B40 6LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	118011
5°	110362
10°	90006
15°	66238
20°	45650
25°	33891
30°	25460
35°	15874
40°	7707
45°	2644
50°	341
55°	258
60°	153
65°	182
70°	224
75°	0
80°	0
85°	0



TEST NUMBER: P843990

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B40 6LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	179.0	18.9
10°-20°	321.3	34.0
20°-30°	259.7	27.5
30°-40°	149.6	15.8
40°-50°	31.6	3.3
50°-60°	2.7	0.3
60°-70°	1.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	760.0	80.4
0°-40°	909.6	96.2
0°-60°	944.0	99.8
0°-90°	945.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	945.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2153	
5°	2006	179
15°	1167	321
25°	560	260
35°	237	150
45°	34	32
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P843990

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B40 6LBNLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2152.7
2.5°	2126.9
5°	2005.5
7.5°	1831.0
10°	1616.9
12.5°	1397.5
15°	1167.1
17.5°	944.8
20°	782.5
22.5°	658.5
25°	560.3
27.5°	477.2
30°	402.2
32.5°	319.1
35°	237.2
37.5°	165.0
40°	107.7
42.5°	65.5
45°	34.1
47.5°	13.6
50°	4.0
52.5°	4.0
55°	2.7
57.5°	2.7
60°	1.4
62.5°	1.4
65°	1.4
67.5°	1.4
70°	1.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)