

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245611

Luminaire Tested: **LSR8B15D010 EC8B15835 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245611
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201794)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15835 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: 2183 (1 lamp)
Luminaire Lumens: 1271.1 lumens
Efficiency: 58.2%
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245611

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245611

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	69	69	69	69	68	68	68	68	65	65	65	62	62	62	59	59	59	58
1	66	65	63	62	65	64	62	61	61	60	59	59	58	58	57	57	56	55
2	63	61	59	57	62	60	58	56	58	56	55	56	55	54	55	54	53	52
3	60	57	54	52	59	56	54	52	55	53	51	53	52	50	52	51	49	49
4	58	54	51	48	57	53	50	48	52	49	48	51	49	47	50	48	47	46
5	55	51	47	45	54	50	47	45	49	47	45	48	46	44	47	45	44	43
6	53	48	45	42	52	47	44	42	47	44	42	46	43	42	45	43	41	41
7	50	45	42	40	50	45	42	40	44	41	39	43	41	39	43	41	39	38
8	48	43	40	37	47	43	40	37	42	39	37	41	39	37	41	39	37	36
9	46	41	38	35	45	40	37	35	40	37	35	39	37	35	39	37	35	34
10	44	39	36	34	43	39	36	34	38	35	33	38	35	33	37	35	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62576
5°	61571
10°	54708
15°	45141
20°	38000
25°	32061
30°	24002
35°	13574
40°	5362
45°	1443
50°	278
55°	0
60°	37
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P245611

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBN0GPH

ZONAL LUMENS:

CANDELA DISTRIBUTION:

Zone	Lumens	% Fixture	% Lamp	0°	Flux	
0°-10°	182.0	14.3	8.3	0°	2029	
10°-20°	396.7	31.2	18.2	5°	1989	182
20°-30°	425.0	33.4	19.5	15°	1414	397
30°-40°	230.3	18.1	10.5	25°	942	425
40°-50°	35.9	2.8	1.6	35°	361	230
50°-60°	1.0	0.1	0.0	45°	33	36
60°-70°	0.2	0.0	0.0	55°	0	1
70°-80°	0.0	0.0	0.0	65°	0	0
80°-90°	0.0	0.0	0.0	75°	0	0
90°-100°	0.0	0.0	0.0	85°	0	0
100°-110°	0.0	0.0	0.0	90°	0	0
110°-120°	0.0	0.0	0.0	95°	0	0
120°-130°	0.0	0.0	0.0	105°	0	0
130°-140°	0.0	0.0	0.0	115°	0	0
140°-150°	0.0	0.0	0.0	125°	0	0
150°-160°	0.0	0.0	0.0	135°	0	0
160°-170°	0.0	0.0	0.0	145°	0	0
170°-180°	0.0	0.0	0.0	155°	0	0
0°-30°	1003.7	79.0	46.0	165°	0	0
0°-40°	1234.0	97.1	56.5	175°	0	0
0°-60°	1270.8	100.0	58.2	180°	0	0
0°-90°	1271.1	100.0	58.2			
90°-120°	0.0	0.0	0.0			
90°-150°	0.0	0.0	0.0			
90°-180°	0.0	0.0	0.0			
0°-180°	1271.1	100.0	58.2			



TEST NUMBER: P245611

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBN0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2029.3
2.5°	2027.6
5°	1989.1
7.5°	1894.3
10°	1747.2
12.5°	1575.0
15°	1414.0
17.5°	1277.2
20°	1158.0
22.5°	1051.0
25°	942.3
27.5°	818.9
30°	674.1
32.5°	514.1
35°	360.6
37.5°	231.0
40°	133.2
42.5°	71.0
45°	33.1
47.5°	18.1
50°	5.8
52.5°	0.6
55°	0.0
57.5°	0.6
60°	0.6
62.5°	0.0
65°	0.0
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245611

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBN0GPH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)