

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243883

Luminaire Tested: **LSR8B15D010 EC8B15835 8LBN0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243883
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15835 8LBNOLI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1501.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243883

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243883

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBNOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226767
5°	157501
10°	82880
15°	52439
20°	38971
25°	30639
30°	22058
35°	9468
40°	3301
45°	1265
50°	293
55°	108
60°	0
65°	146
70°	45
75°	119
80°	178
85°	0



TEST NUMBER: P243883

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBNOLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	407.9	27.2
10°-20°	474.0	31.6
20°-30°	409.1	27.3
30°-40°	177.5	11.8
40°-50°	27.8	1.9
50°-60°	2.0	0.1
60°-70°	1.1	0.1
70°-80°	1.1	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1290.9	86.0
0°-40°	1468.4	97.8
0°-60°	1498.2	99.8
0°-90°	1501.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1501.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7354	
5°	5088	408
15°	1643	474
25°	900	409
35°	252	177
45°	29	28
55°	2	2
65°	2	1
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P243883

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBNOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7353.9
2.5°	6640.8
5°	5088.2
7.5°	3628.8
10°	2646.9
12.5°	2031.0
15°	1642.6
17.5°	1381.5
20°	1187.6
22.5°	1022.1
25°	900.5
27.5°	772.2
30°	619.5
32.5°	430.6
35°	251.5
37.5°	140.5
40°	82.0
42.5°	50.9
45°	29.0
47.5°	23.4
50°	6.1
52.5°	3.1
55°	2.0
57.5°	1.0
60°	0.0
62.5°	0.5
65°	2.0
67.5°	1.5
70°	0.5
72.5°	2.5
75°	1.0
77.5°	0.0
80°	1.0
82.5°	0.5
85°	0.0
87.5°	1.0
90°	0.0

(END OF REPORT)