

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843996

Luminaire Tested: **LD6C10DE010B2750 EU6C10B50 6LBCSMMS**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843996
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204757)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C10DE010B2750 EU6C10B50 6LBCSMMS
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1305.1 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843996

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B50 6LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P843996

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B50 6LBSCMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 110 | 106 | 102 | 99 | 108 | 104 | 100 | 97 | 100 | 97 | 94 | 96 | 93 | 91 | 92 | 90 | 89 | 87 | | | | 87 |
| 2 | 101 | 94 | 87 | 82 | 99 | 92 | 86 | 81 | 88 | 84 | 79 | 85 | 81 | 78 | 82 | 79 | 76 | 74 | | | | 74 |
| 3 | 93 | 83 | 75 | 70 | 90 | 81 | 74 | 69 | 79 | 73 | 68 | 76 | 71 | 67 | 73 | 69 | 65 | 63 | | | | 63 |
| 4 | 85 | 74 | 66 | 60 | 83 | 73 | 65 | 59 | 70 | 64 | 58 | 68 | 62 | 58 | 66 | 61 | 57 | 55 | | | | 55 |
| 5 | 79 | 66 | 58 | 52 | 77 | 65 | 57 | 51 | 63 | 56 | 51 | 61 | 55 | 50 | 60 | 54 | 50 | 48 | | | | 48 |
| 6 | 73 | 60 | 52 | 45 | 71 | 59 | 51 | 45 | 57 | 50 | 45 | 56 | 49 | 44 | 54 | 49 | 44 | 42 | | | | 42 |
| 7 | 68 | 55 | 46 | 40 | 66 | 54 | 46 | 40 | 52 | 45 | 40 | 51 | 44 | 40 | 50 | 44 | 39 | 37 | | | | 37 |
| 8 | 63 | 50 | 42 | 36 | 61 | 49 | 41 | 36 | 48 | 41 | 36 | 47 | 40 | 36 | 46 | 40 | 35 | 33 | | | | 33 |
| 9 | 59 | 46 | 38 | 33 | 57 | 45 | 38 | 32 | 44 | 37 | 32 | 43 | 37 | 32 | 42 | 36 | 32 | 30 | | | | 30 |
| 10 | 55 | 42 | 35 | 30 | 54 | 42 | 34 | 30 | 41 | 34 | 29 | 40 | 34 | 29 | 39 | 33 | 29 | 27 | | | | 27 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 29230 |
| 5° | 29199 |
| 10° | 29191 |
| 15° | 28910 |
| 20° | 28702 |
| 25° | 28417 |
| 30° | 27928 |
| 35° | 27479 |
| 40° | 26657 |
| 45° | 25755 |
| 50° | 24221 |
| 55° | 21925 |
| 60° | 19253 |
| 65° | 16201 |
| 70° | 12678 |
| 75° | 8896 |
| 80° | 4988 |
| 85° | 3459 |



TEST NUMBER: P843996

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B50 6LBCSMMS

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 50.5 | 3.9 |
| 10°-20° | 143.8 | 11.0 |
| 20°-30° | 216.3 | 16.6 |
| 30°-40° | 256.4 | 19.6 |
| 40°-50° | 255.1 | 19.5 |
| 50°-60° | 205.6 | 15.8 |
| 60°-70° | 124.4 | 9.5 |
| 70°-80° | 46.2 | 3.5 |
| 80°-90° | 6.8 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 410.6 | 31.5 |
| 0°-40° | 666.9 | 51.1 |
| 0°-60° | 1127.7 | 86.4 |
| 0°-90° | 1305.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1305.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 533 | |
| 5° | 531 | 51 |
| 15° | 509 | 144 |
| 25° | 470 | 216 |
| 35° | 411 | 256 |
| 45° | 332 | 255 |
| 55° | 229 | 206 |
| 65° | 125 | 124 |
| 75° | 42 | 46 |
| 85° | 6 | 7 |
| 90° | 0 | |



TEST NUMBER: P843996

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B50 6LBCSMMS

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 533.2 |
| 2.5° | 533.2 |
| 5° | 530.6 |
| 7.5° | 529.1 |
| 10° | 524.4 |
| 12.5° | 516.4 |
| 15° | 509.4 |
| 17.5° | 501.4 |
| 20° | 492.0 |
| 22.5° | 482.4 |
| 25° | 469.8 |
| 27.5° | 456.4 |
| 30° | 441.2 |
| 32.5° | 427.1 |
| 35° | 410.6 |
| 37.5° | 393.1 |
| 40° | 372.5 |
| 42.5° | 352.7 |
| 45° | 332.2 |
| 47.5° | 309.3 |
| 50° | 284.0 |
| 52.5° | 257.7 |
| 55° | 229.4 |
| 57.5° | 204.0 |
| 60° | 175.6 |
| 62.5° | 150.3 |
| 65° | 124.9 |
| 67.5° | 101.2 |
| 70° | 79.1 |
| 72.5° | 59.3 |
| 75° | 42.0 |
| 77.5° | 26.9 |
| 80° | 15.8 |
| 82.5° | 9.4 |
| 85° | 5.5 |
| 87.5° | 2.3 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)