

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844007

Luminaire Tested: **LD6C10DE010B2750 EU6C10B50 6LBNLI**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P844007  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C10DE010B2750 EU6C10B50 6LBNLI  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1009.1 lumens  
Efficiency: N/A  
Efficacy: 75.9 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844007

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B50 6LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P844007

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B50 6LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	125933
5°	117769
10°	96046
15°	70681
20°	48718
25°	36171
30°	27169
35°	16938
40°	8230
45°	2822
50°	367
55°	287
60°	164
65°	195
70°	240
75°	0
80°	0
85°	0



TEST NUMBER: P844007

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B50 6LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	191.0	18.9
10°-20°	342.8	34.0
20°-30°	277.2	27.5
30°-40°	159.7	15.8
40°-50°	33.7	3.3
50°-60°	2.9	0.3
60°-70°	1.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	811.0	80.4
0°-40°	970.7	96.2
0°-60°	1007.4	99.8
0°-90°	1009.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1009.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2297	
5°	2140	191
15°	1245	343
25°	598	277
35°	253	160
45°	36	34
55°	3	3
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P844007

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B50 6LBNLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2297.2
2.5°	2269.6
5°	2140.1
7.5°	1953.9
10°	1725.4
12.5°	1491.3
15°	1245.4
17.5°	1008.2
20°	835.1
22.5°	702.7
25°	598.0
27.5°	509.3
30°	429.2
32.5°	340.5
35°	253.1
37.5°	176.0
40°	115.0
42.5°	69.8
45°	36.4
47.5°	14.5
50°	4.3
52.5°	4.3
55°	3.0
57.5°	3.0
60°	1.5
62.5°	1.5
65°	1.5
67.5°	1.5
70°	1.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)