

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244687

Luminaire Tested: **LSR8B15D010 EC8B15850 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244687  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B15D010 EC8B15850 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 5000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1512.0 lumens  
Efficiency: N/A  
Efficacy: 105.0 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244687

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244687

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	33790
5°	33109
10°	32060
15°	31630
20°	31440
25°	31044
30°	29376
35°	24228
40°	15127
45°	9729
50°	7546
55°	5806
60°	4397
65°	2860
70°	1226
75°	596
80°	266
85°	177



TEST NUMBER: P244687

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.6	6.7
10°-20°	279.9	18.5
20°-30°	416.9	27.6
30°-40°	387.2	25.6
40°-50°	182.9	12.1
50°-60°	98.2	6.5
60°-70°	39.5	2.6
70°-80°	6.2	0.4
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	797.4	52.7
0°-40°	1184.6	78.3
0°-60°	1465.7	96.9
0°-90°	1512.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1512.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1096	
5°	1070	101
15°	991	280
25°	912	417
35°	644	387
45°	223	183
55°	108	98
65°	39	39
75°	5	6
85°	0	1
90°	0	



TEST NUMBER: P244687

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1095.8
2.5°	1088.2
5°	1069.6
7.5°	1046.0
10°	1023.9
12.5°	1005.8
15°	990.8
17.5°	975.2
20°	958.1
22.5°	938.5
25°	912.4
27.5°	875.7
30°	825.0
32.5°	750.6
35°	643.6
37.5°	506.9
40°	375.8
42.5°	279.8
45°	223.1
47.5°	186.4
50°	157.3
52.5°	131.1
55°	108.0
57.5°	87.9
60°	71.3
62.5°	55.8
65°	39.2
67.5°	23.1
70°	13.6
72.5°	8.0
75°	5.0
77.5°	3.0
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)