

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245803

Luminaire Tested: **LSR8B15D010 EC8B15927 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245803
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15927 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1194.7 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245803

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245803

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45	55	49	45	54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P245803

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.5	5.4
10°-20°	182.5	15.3
20°-30°	271.7	22.7
30°-40°	308.9	25.9
40°-50°	252.6	21.1
50°-60°	94.2	7.9
60°-70°	17.2	1.4
70°-80°	2.7	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.8	43.4
0°-40°	827.7	69.3
0°-60°	1174.5	98.3
0°-90°	1194.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1194.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	686	
5°	681	65
15°	647	183
25°	591	272
35°	496	309
45°	336	253
55°	97	94
65°	16	17
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P245803

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	685.8
2.5°	684.6
5°	681.1
7.5°	674.9
10°	666.7
12.5°	657.3
15°	647.2
17.5°	635.5
20°	623.0
22.5°	608.2
25°	591.1
27.5°	571.5
30°	549.3
32.5°	524.0
35°	495.9
37.5°	465.9
40°	431.2
42.5°	388.3
45°	336.0
47.5°	273.3
50°	207.4
52.5°	146.2
55°	96.6
57.5°	60.9
60°	37.8
62.5°	24.2
65°	15.6
67.5°	9.0
70°	5.1
72.5°	3.2
75°	2.4
77.5°	1.6
80°	1.1
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)