

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844036

Luminaire Tested: **LD6C15DE010B2750 EU6C15B30 6LBMGPH**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P844036
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C15DE010B2750 EU6C15B30 6LBMGPH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 843.0 lumens
Efficiency: N/A
Efficacy: 49.6 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844036

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBMGPH

Luminous Intensity Polar Plot





TEST NUMBER: P844036

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBMGPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34482
5°	34036
10°	32876
15°	31476
20°	29910
25°	27848
30°	23991
35°	18203
40°	13311
45°	10094
50°	8239
55°	7216
60°	6633
65°	6032
70°	5402
75°	4935
80°	4420
85°	3648



TEST NUMBER: P844036

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBMGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	6.9
10°-20°	155.6	18.5
20°-30°	209.0	24.8
30°-40°	171.4	20.3
40°-50°	102.9	12.2
50°-60°	68.4	8.1
60°-70°	45.9	5.4
70°-80°	24.7	2.9
80°-90°	7.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.7	50.1
0°-40°	594.1	70.5
0°-60°	765.5	90.8
0°-90°	843.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	843.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	629	
5°	618	58
15°	555	156
25°	460	209
35°	272	171
45°	130	103
55°	76	68
65°	46	46
75°	23	25
85°	6	7
90°	0	



TEST NUMBER: P844036

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBMGPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	629.0
2.5°	624.3
5°	618.5
7.5°	605.7
10°	590.6
12.5°	572.0
15°	554.6
17.5°	533.7
20°	512.7
22.5°	489.5
25°	460.4
27.5°	425.5
30°	379.0
32.5°	326.7
35°	272.0
37.5°	225.6
40°	186.0
42.5°	154.6
45°	130.2
47.5°	110.4
50°	96.6
52.5°	84.8
55°	75.5
57.5°	67.5
60°	60.5
62.5°	52.4
65°	46.5
67.5°	39.6
70°	33.7
72.5°	27.9
75°	23.3
77.5°	18.6
80°	14.0
82.5°	10.5
85°	5.8
87.5°	2.3
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)