

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246307

Luminaire Tested: **LSR8B15D010 EC8B15927 8LBW0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246307  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B15D010 EC8B15927 8LBW0B  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 2700 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 777.4 lumens  
Efficiency: N/A  
Efficacy: 54.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246307

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBW0B

### Luminous Intensity Polar Plot





TEST NUMBER: P246307

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBW0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93						
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86						
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80						
4	96	88	83	78	94	87	82	78	85	80	77	83	79	76	81	78	75	74						
5	91	82	76	72	89	81	76	71	80	75	71	78	74	70	76	73	70	68						
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	65	63						
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58						
8	77	67	61	57	76	67	61	57	66	60	56	65	60	56	64	59	56	54						
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51						
10	70	59	53	49	68	59	53	49	58	53	49	57	52	49	57	52	49	47						

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P246307

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBW0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.1	8.4
10°-20°	179.9	23.1
20°-30°	256.9	33.1
30°-40°	212.9	27.4
40°-50°	52.5	6.8
50°-60°	9.5	1.2
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	502.0	64.6
0°-40°	714.9	92.0
0°-60°	776.9	99.9
0°-90°	777.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	777.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	711	
5°	690	65
15°	639	180
25°	564	257
35°	358	213
45°	56	53
55°	9	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246307

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBW0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	710.9
2.5°	704.9
5°	690.3
7.5°	676.1
10°	664.3
12.5°	652.8
15°	639.4
17.5°	623.6
20°	605.9
22.5°	585.8
25°	563.6
27.5°	533.7
30°	494.2
32.5°	438.5
35°	358.4
37.5°	259.0
40°	159.4
42.5°	92.8
45°	56.0
47.5°	37.1
50°	24.9
52.5°	16.2
55°	9.1
57.5°	4.4
60°	2.0
62.5°	0.8
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)