

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844037

Luminaire Tested: **LD6C15DE010B2750 EU6C15B30 6LBMH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844037
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C15DE010B2750 EU6C15B30 6LBMH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1105.2 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844037

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P844037

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59962
5°	58887
10°	55877
15°	52401
20°	48800
25°	44966
30°	37468
35°	26408
40°	16832
45°	10040
50°	5927
55°	3766
60°	2598
65°	1842
70°	1266
75°	1017
80°	505
85°	0



TEST NUMBER: P844037

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.0	9.0
10°-20°	258.7	23.4
20°-30°	335.2	30.3
30°-40°	248.9	22.5
40°-50°	105.1	9.5
50°-60°	37.3	3.4
60°-70°	14.4	1.3
70°-80°	5.0	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	694.0	62.8
0°-40°	942.9	85.3
0°-60°	1085.2	98.2
0°-90°	1105.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1105.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1094	
5°	1070	100
15°	923	259
25°	743	335
35°	395	249
45°	130	105
55°	39	37
65°	14	14
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P844037

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1093.8
2.5°	1090.6
5°	1070.1
7.5°	1040.1
10°	1003.8
12.5°	964.4
15°	923.3
17.5°	877.5
20°	836.5
22.5°	793.9
25°	743.4
27.5°	673.9
30°	591.9
32.5°	495.6
35°	394.6
37.5°	309.4
40°	235.2
42.5°	175.1
45°	129.5
47.5°	94.7
50°	69.5
52.5°	52.0
55°	39.4
57.5°	29.9
60°	23.7
62.5°	17.3
65°	14.2
67.5°	11.0
70°	7.9
72.5°	6.2
75°	4.8
77.5°	3.2
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)