

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844061

Luminaire Tested: **LD6C15DE010B2750 EU6C15B35 6LBWH**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P844061  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C15DE010B2750 EU6C15B35 6LBWH  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1372.8 lumens  
Efficiency: N/A  
Efficacy: 80.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 17  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844061

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B35 6LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P844061

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B35 6LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59		
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41		
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	46416
5°	46395
10°	46047
15°	45732
20°	45037
25°	44005
30°	41437
35°	37497
40°	31309
45°	23995
50°	16997
55°	10714
60°	6041
65°	3917
70°	2565
75°	1885
80°	1137
85°	1132



TEST NUMBER: P844061

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B35 6LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.0	5.8
10°-20°	226.9	16.5
20°-30°	332.7	24.2
30°-40°	346.2	25.2
40°-50°	239.6	17.5
50°-60°	104.3	7.6
60°-70°	32.0	2.3
70°-80°	9.6	0.7
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	639.6	46.6
0°-40°	985.8	71.8
0°-60°	1329.7	96.9
0°-90°	1372.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1372.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	847	
5°	843	80
15°	806	227
25°	728	333
35°	560	346
45°	310	240
55°	112	104
65°	30	32
75°	9	10
85°	2	1
90°	0	



TEST NUMBER: P844061

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B35 6LBWH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	846.7
2.5°	848.5
5°	843.1
7.5°	836.1
10°	827.2
12.5°	818.3
15°	805.8
17.5°	789.7
20°	772.0
22.5°	752.4
25°	727.5
27.5°	695.5
30°	654.6
32.5°	611.8
35°	560.3
37.5°	503.4
40°	437.5
42.5°	371.8
45°	309.5
47.5°	250.8
50°	199.3
52.5°	151.2
55°	112.1
57.5°	80.1
60°	55.1
62.5°	40.9
65°	30.2
67.5°	23.2
70°	16.0
72.5°	12.5
75°	8.9
77.5°	5.3
80°	3.6
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)