

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844063

Luminaire Tested: **LD6C15DE010B2750 EU6C15B40 6LBCSMB**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P844063
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204757)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C15DE010B2750 EU6C15B40 6LBCSMB
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1427.8 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844063

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B40 6LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P844063

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B40 6LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31971
5°	31945
10°	31936
15°	31629
20°	31398
25°	31084
30°	30555
35°	30055
40°	29169
45°	28181
50°	26490
55°	23990
60°	21062
65°	17719
70°	13865
75°	9722
80°	5430
85°	3774



TEST NUMBER: P844063

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B40 6LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.2	3.9
10°-20°	157.3	11.0
20°-30°	236.6	16.6
30°-40°	280.4	19.6
40°-50°	279.1	19.5
50°-60°	225.0	15.8
60°-70°	136.1	9.5
70°-80°	50.5	3.5
80°-90°	7.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	449.2	31.5
0°-40°	729.6	51.1
0°-60°	1233.7	86.4
0°-90°	1427.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1427.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	583	
5°	580	55
15°	557	157
25°	514	237
35°	449	280
45°	364	279
55°	251	225
65°	137	136
75°	46	51
85°	6	7
90°	0	



TEST NUMBER: P844063

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B40 6LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	583.2
2.5°	583.2
5°	580.5
7.5°	578.8
10°	573.7
12.5°	565.0
15°	557.3
17.5°	548.6
20°	538.2
22.5°	527.8
25°	513.9
27.5°	499.2
30°	482.7
32.5°	467.3
35°	449.1
37.5°	430.0
40°	407.6
42.5°	385.8
45°	363.5
47.5°	338.2
50°	310.6
52.5°	282.1
55°	251.0
57.5°	223.3
60°	192.1
62.5°	164.4
65°	136.6
67.5°	110.7
70°	86.5
72.5°	64.9
75°	45.9
77.5°	29.4
80°	17.2
82.5°	10.4
85°	6.0
87.5°	2.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)