

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244069

Luminaire Tested: **LSR8B15D010 EC8B15950 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15950 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1592.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244069

CATALOG NUMBER: LSR8B15D010 EC8B15950 8LBS0LI

Luminous Intensity Polar Plot





TEST NUMBER: P244069

CATALOG NUMBER: LSR8B15D010 EC8B15950 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91					91			
2	105	99	95	91	103	98	93	90	94	91	88	91	88	86	88	86	84	82					82			
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74					74			
4	92	83	76	71	90	82	75	71	79	74	70	77	73	69	75	71	68	66					66			
5	86	76	69	63	84	75	68	63	73	67	63	71	66	62	69	65	61	60					60			
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54					54			
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49					49			
8	71	59	52	47	69	58	52	47	57	51	47	56	51	46	55	50	46	45					45			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41					41			
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37					37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27370
5°	27490
10°	27937
15°	28642
20°	29143
25°	29176
30°	28272
35°	25884
40°	22498
45°	17801
50°	11542
55°	5769
60°	2424
65°	1065
70°	334
75°	167
80°	160
85°	177



TEST NUMBER: P244069

CATALOG NUMBER: LSR8B15D010 EC8B15950 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.9	5.3
10°-20°	253.5	15.9
20°-30°	392.8	24.7
30°-40°	426.5	26.8
40°-50°	310.0	19.5
50°-60°	105.3	6.6
60°-70°	16.8	1.1
70°-80°	1.8	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	731.2	45.9
0°-40°	1157.7	72.7
0°-60°	1573.1	98.8
0°-90°	1592.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1592.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	888	
5°	888	85
15°	897	254
25°	858	393
35°	688	427
45°	408	310
55°	107	105
65°	15	17
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P244069

CATALOG NUMBER: LSR8B15D010 EC8B15950 8LBS0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	887.6
2.5°	887.6
5°	888.1
7.5°	889.5
10°	892.2
12.5°	895.4
15°	897.2
17.5°	895.4
20°	888.1
22.5°	874.8
25°	857.5
27.5°	831.5
30°	794.0
32.5°	744.3
35°	687.6
37.5°	626.0
40°	558.9
42.5°	486.3
45°	408.2
47.5°	324.2
50°	240.6
52.5°	164.8
55°	107.3
57.5°	65.3
60°	39.3
62.5°	24.2
65°	14.6
67.5°	8.2
70°	3.7
72.5°	2.3
75°	1.4
77.5°	0.9
80°	0.9
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)