

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844082

Luminaire Tested: **LD6C15DE010B2750 EU6C15B50 6LBCSMW**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P844082
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204757)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C15DE010B2750 EU6C15B50 6LBSCMW
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1804.4 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844082

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B50 6LBCSMW

Luminous Intensity Polar Plot





TEST NUMBER: P844082

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B50 6LBSCMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40408
5°	40375
10°	40352
15°	39972
20°	39682
25°	39287
30°	38614
35°	37979
40°	36862
45°	35608
50°	33483
55°	30317
60°	26599
65°	22402
70°	17535
75°	12285
80°	6882
85°	4780



TEST NUMBER: P844082

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B50 6LBCSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.8	3.9
10°-20°	198.8	11.0
20°-30°	299.0	16.6
30°-40°	354.4	19.6
40°-50°	352.7	19.5
50°-60°	284.3	15.8
60°-70°	171.9	9.5
70°-80°	63.9	3.5
80°-90°	9.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	567.6	31.5
0°-40°	922.1	51.1
0°-60°	1559.1	86.4
0°-90°	1804.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1804.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	737	
5°	734	70
15°	704	199
25°	650	299
35°	568	354
45°	459	353
55°	317	284
65°	173	172
75°	58	64
85°	8	9
90°	0	



TEST NUMBER: P844082

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B50 6LBCSMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	737.1
2.5°	737.1
5°	733.7
7.5°	731.6
10°	724.9
12.5°	713.9
15°	704.3
17.5°	693.3
20°	680.2
22.5°	666.9
25°	649.5
27.5°	630.9
30°	610.0
32.5°	590.5
35°	567.5
37.5°	543.5
40°	515.1
42.5°	487.6
45°	459.3
47.5°	427.5
50°	392.6
52.5°	356.4
55°	317.2
57.5°	282.1
60°	242.6
62.5°	207.7
65°	172.7
67.5°	139.9
70°	109.4
72.5°	82.1
75°	58.0
77.5°	37.1
80°	21.8
82.5°	13.1
85°	7.6
87.5°	3.3
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)