

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844092

Luminaire Tested: **LD6C15DE010B2750 EU6C15B50 6LBNLI**

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P844092  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C15DE010B2750 EU6C15B50 6LBNI  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1306.2 lumens  
Efficiency: N/A  
Efficacy: 76.8 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 17  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844092

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B50 6LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P844092

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B50 6LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	163030
5°	152459
10°	124341
15°	91504
20°	63064
25°	46823
30°	35170
35°	21931
40°	10649
45°	3652
50°	478
55°	363
60°	208
65°	246
70°	305
75°	0
80°	0
85°	0



TEST NUMBER: P844092

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B50 6LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	247.3	18.9
10°-20°	443.8	34.0
20°-30°	358.8	27.5
30°-40°	206.7	15.8
40°-50°	43.7	3.3
50°-60°	3.8	0.3
60°-70°	1.9	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1049.9	80.4
0°-40°	1256.6	96.2
0°-60°	1304.1	99.8
0°-90°	1306.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1306.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2974	
5°	2770	247
15°	1612	444
25°	774	359
35°	328	207
45°	47	44
55°	4	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P844092

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B50 6LBNLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2973.9
2.5°	2938.1
5°	2770.5
7.5°	2529.4
10°	2233.7
12.5°	1930.5
15°	1612.3
17.5°	1305.2
20°	1081.0
22.5°	909.7
25°	774.1
27.5°	659.2
30°	555.6
32.5°	440.7
35°	327.7
37.5°	227.9
40°	148.8
42.5°	90.4
45°	47.1
47.5°	18.8
50°	5.6
52.5°	5.6
55°	3.8
57.5°	3.8
60°	1.9
62.5°	1.9
65°	1.9
67.5°	1.9
70°	1.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)