

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844104

Luminaire Tested: **LD6C20DE010B2750 EU6C20B27 6LBMGPH**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P844104
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C20DE010B2750 EU6C20B27 6LBMGPH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1082.0 lumens
Efficiency: N/A
Efficacy: 49.6 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844104

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B27 6LBMGPH

Luminous Intensity Polar Plot





TEST NUMBER: P844104

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B27 6LBMGPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44256
5°	43688
10°	42200
15°	40398
20°	38393
25°	35742
30°	30796
35°	23370
40°	17082
45°	12955
50°	10558
55°	9271
60°	8508
65°	7757
70°	6940
75°	6312
80°	5651
85°	4655



TEST NUMBER: P844104

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B27 6LBMGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	6.9
10°-20°	199.8	18.5
20°-30°	268.2	24.8
30°-40°	220.0	20.3
40°-50°	132.1	12.2
50°-60°	87.8	8.1
60°-70°	58.9	5.4
70°-80°	31.7	2.9
80°-90°	8.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	542.6	50.1
0°-40°	762.6	70.5
0°-60°	982.5	90.8
0°-90°	1082.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1082.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	807	
5°	794	75
15°	712	200
25°	591	268
35°	349	220
45°	167	132
55°	97	88
65°	60	59
75°	30	32
85°	7	9
90°	0	



TEST NUMBER: P844104

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B27 6LBMGPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	807.3
2.5°	801.4
5°	793.9
7.5°	777.5
10°	758.1
12.5°	734.2
15°	711.8
17.5°	684.9
20°	658.1
22.5°	628.2
25°	590.9
27.5°	546.2
30°	486.5
32.5°	419.4
35°	349.2
37.5°	289.5
40°	238.7
42.5°	198.5
45°	167.1
47.5°	141.7
50°	123.8
52.5°	108.9
55°	97.0
57.5°	86.5
60°	77.6
62.5°	67.2
65°	59.8
67.5°	50.8
70°	43.3
72.5°	35.9
75°	29.8
77.5°	23.9
80°	17.9
82.5°	13.4
85°	7.4
87.5°	3.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)