

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844112

Luminaire Tested: **LD6C20DE010B2750 EU6C20B27 6LBWH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844112
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C20DE010B2750 EU6C20B27 6LBWH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1715.5 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844112

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B27 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P844112

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B27 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58005
5°	57979
10°	57536
15°	57151
20°	56279
25°	54989
30°	51780
35°	46866
40°	39130
45°	29988
50°	21236
55°	13381
60°	7554
65°	4903
70°	3206
75°	2351
80°	1389
85°	1384



TEST NUMBER: P844112

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B27 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	5.8
10°-20°	283.6	16.5
20°-30°	415.8	24.2
30°-40°	432.7	25.2
40°-50°	299.4	17.5
50°-60°	130.4	7.6
60°-70°	40.0	2.3
70°-80°	12.0	0.7
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	799.3	46.6
0°-40°	1232.0	71.8
0°-60°	1661.7	96.9
0°-90°	1715.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1715.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1058	
5°	1054	100
15°	1007	284
25°	909	416
35°	700	433
45°	387	299
55°	140	130
65°	38	40
75°	11	12
85°	2	2
90°	0	



TEST NUMBER: P844112

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B27 6LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1058.1
2.5°	1060.3
5°	1053.6
7.5°	1044.7
10°	1033.6
12.5°	1022.5
15°	1007.0
17.5°	986.9
20°	964.7
22.5°	940.2
25°	909.1
27.5°	869.2
30°	818.0
32.5°	764.7
35°	700.3
37.5°	629.1
40°	546.8
42.5°	464.6
45°	386.8
47.5°	313.4
50°	249.0
52.5°	189.0
55°	140.0
57.5°	100.1
60°	68.9
62.5°	51.2
65°	37.8
67.5°	28.9
70°	20.0
72.5°	15.5
75°	11.1
77.5°	6.7
80°	4.4
82.5°	2.2
85°	2.2
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)