

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844140

Luminaire Tested: **LD6C20DE010B2750 EU6C20B35 6LBMLI**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P844140  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C20DE010B2750 EU6C20B35 6LBMLI  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1755.6 lumens  
Efficiency: N/A  
Efficacy: 80.5 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844140

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B35 6LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P844140

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B35 6LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	120445
5°	119299
10°	113052
15°	102634
20°	90693
25°	78410
30°	61294
35°	37584
40°	19293
45°	7667
50°	2490
55°	860
60°	735
65°	584
70°	353
75°	466
80°	0
85°	0



TEST NUMBER: P844140

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B35 6LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.4	11.5
10°-20°	503.9	28.7
20°-30°	585.8	33.4
30°-40°	358.7	20.4
40°-50°	89.1	5.1
50°-60°	10.4	0.6
60°-70°	3.9	0.2
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1292.1	73.6
0°-40°	1650.8	94.0
0°-60°	1750.3	99.7
0°-90°	1755.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1755.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2197	
5°	2168	202
15°	1808	504
25°	1296	586
35°	562	359
45°	99	89
55°	9	10
65°	4	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P844140

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B35 6LBMLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2197.1
2.5°	2194.9
5°	2167.9
7.5°	2109.6
10°	2030.9
12.5°	1927.5
15°	1808.4
17.5°	1680.5
20°	1554.6
22.5°	1428.8
25°	1296.3
27.5°	1143.5
30°	968.3
32.5°	763.8
35°	561.6
37.5°	395.3
40°	269.6
42.5°	168.5
45°	98.9
47.5°	56.2
50°	29.2
52.5°	13.5
55°	9.0
57.5°	6.7
60°	6.7
62.5°	4.5
65°	4.5
67.5°	2.2
70°	2.2
72.5°	2.2
75°	2.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)