

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844143

Luminaire Tested: **LD6C20DE010B2750 EU6C20B35 6LBNLI**

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P844143  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C20DE010B2750 EU6C20B35 6LBNI  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1559.9 lumens  
Efficiency: N/A  
Efficacy: 71.6 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844143

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B35 6LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P844143

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B35 6LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	194705
5°	182087
10°	148505
15°	109280
20°	75327
25°	55921
30°	42006
35°	26194
40°	12717
45°	4365
50°	571
55°	430
60°	241
65°	285
70°	353
75°	0
80°	0
85°	0



TEST NUMBER: P844143

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B35 6LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	295.3	18.9
10°-20°	530.0	34.0
20°-30°	428.6	27.5
30°-40°	246.9	15.8
40°-50°	52.2	3.3
50°-60°	4.5	0.3
60°-70°	2.2	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1253.9	80.4
0°-40°	1500.8	96.2
0°-60°	1557.4	99.8
0°-90°	1559.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1559.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3552	
5°	3309	295
15°	1926	530
25°	924	429
35°	391	247
45°	56	52
55°	4	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P844143

CATALOG NUMBER: LD6C20DE010B2750 EU6C20B35 6LBNLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3551.7
2.5°	3509.1
5°	3308.9
7.5°	3020.9
10°	2667.8
12.5°	2305.6
15°	1925.5
17.5°	1558.8
20°	1291.2
22.5°	1086.5
25°	924.5
27.5°	787.3
30°	663.6
32.5°	526.4
35°	391.4
37.5°	272.1
40°	177.7
42.5°	108.0
45°	56.3
47.5°	22.4
50°	6.7
52.5°	6.7
55°	4.5
57.5°	4.5
60°	2.2
62.5°	2.2
65°	2.2
67.5°	2.2
70°	2.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)