

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246260

Luminaire Tested: **LSR8B20D010 EC8B20835 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246260
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B20D010 EC8B20835 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1410.0 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246260

CATALOG NUMBER: LSR8B20D010 EC8B20835 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P246260

CATALOG NUMBER: LSR8B20D010 EC8B20835 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77	83	79	76	81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71	78	74	70	76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56	65	60	56	64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49	57	52	49	57	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39760
5°	38761
10°	37728
15°	37026
20°	36061
25°	34783
30°	31914
35°	24472
40°	11641
45°	4435
50°	2164
55°	887
60°	222
65°	51
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246260

CATALOG NUMBER: LSR8B20D010 EC8B20835 8LBW0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.0	8.4
10°-20°	326.4	23.1
20°-30°	466.0	33.1
30°-40°	386.2	27.4
40°-50°	95.2	6.8
50°-60°	17.2	1.2
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	910.4	64.6
0°-40°	1296.6	92.0
0°-60°	1409.0	99.9
0°-90°	1410.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1410.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1289	
5°	1252	118
15°	1160	326
25°	1022	466
35°	650	386
45°	102	95
55°	16	17
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246260

CATALOG NUMBER: LSR8B20D010 EC8B20835 8LBW0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1289.4
2.5°	1278.6
5°	1252.2
7.5°	1226.4
10°	1204.9
12.5°	1184.1
15°	1159.8
17.5°	1131.2
20°	1098.9
22.5°	1062.4
25°	1022.3
27.5°	967.9
30°	896.3
32.5°	795.4
35°	650.1
37.5°	469.6
40°	289.2
42.5°	168.2
45°	101.7
47.5°	67.3
50°	45.1
52.5°	29.4
55°	16.5
57.5°	7.9
60°	3.6
62.5°	1.4
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)