

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243938

Luminaire Tested: **LSR8B20D010 EC8B20930 8LBN0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243938  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B20D010 EC8B20930 8LBNOLI  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1761.1 lumens  
Efficiency: N/A  
Efficacy: 82.7 lumens/watt  
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 21.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243938

CATALOG NUMBER: LSR8B20D010 EC8B20930 8LBNOLI

### Luminous Intensity Polar Plot





TEST NUMBER: P243938

CATALOG NUMBER: LSR8B20D010 EC8B20930 8LBNOLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P243938

CATALOG NUMBER: LSR8B20D010 EC8B20930 8LBNOLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	478.6	27.2
10°-20°	556.1	31.6
20°-30°	479.9	27.3
30°-40°	208.2	11.8
40°-50°	32.7	1.9
50°-60°	2.4	0.1
60°-70°	1.3	0.1
70°-80°	1.3	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1514.6	86.0
0°-40°	1722.8	97.8
0°-60°	1757.9	99.8
0°-90°	1761.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1761.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8628	
5°	5970	479
15°	1927	556
25°	1056	480
35°	295	208
45°	34	33
55°	2	2
65°	2	1
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P243938

CATALOG NUMBER: LSR8B20D010 EC8B20930 8LBNOLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8628.2
2.5°	7791.5
5°	5969.9
7.5°	4257.7
10°	3105.6
12.5°	2382.9
15°	1927.2
17.5°	1620.9
20°	1393.3
22.5°	1199.2
25°	1056.5
27.5°	906.0
30°	726.9
32.5°	505.2
35°	295.0
37.5°	164.8
40°	96.2
42.5°	59.7
45°	34.1
47.5°	27.5
50°	7.2
52.5°	3.6
55°	2.4
57.5°	1.2
60°	0.0
62.5°	0.6
65°	2.4
67.5°	1.8
70°	0.6
72.5°	3.0
75°	1.2
77.5°	0.0
80°	1.2
82.5°	0.6
85°	0.0
87.5°	1.2
90°	0.0

(END OF REPORT)