

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844197

Luminaire Tested: **LD6C25DE010B2750 EU6C25B27 6LBWH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844197
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C25DE010B2750 EU6C25B27 6LBWH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2250.7 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844197

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B27 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P844197

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B27 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76096
5°	76067
10°	75483
15°	74978
20°	73839
25°	72149
30°	67935
35°	61482
40°	51339
45°	39330
50°	27863
55°	17567
60°	9901
65°	6434
70°	4199
75°	3092
80°	1863
85°	1887



TEST NUMBER: P844197

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B27 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.1	5.8
10°-20°	372.0	16.5
20°-30°	545.5	24.2
30°-40°	567.7	25.2
40°-50°	392.8	17.5
50°-60°	171.0	7.6
60°-70°	52.5	2.3
70°-80°	15.7	0.7
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1048.6	46.6
0°-40°	1616.3	71.8
0°-60°	2180.1	96.9
0°-90°	2250.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2250.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1388	
5°	1382	131
15°	1321	372
25°	1193	545
35°	919	568
45°	507	393
55°	184	171
65°	50	52
75°	15	16
85°	3	2
90°	0	



TEST NUMBER: P844197

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B27 6LBWH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1388.1
2.5°	1391.0
5°	1382.3
7.5°	1370.7
10°	1356.0
12.5°	1341.5
15°	1321.1
17.5°	1294.9
20°	1265.7
22.5°	1233.6
25°	1192.8
27.5°	1140.2
30°	1073.2
32.5°	1003.2
35°	918.7
37.5°	825.4
40°	717.4
42.5°	609.5
45°	507.3
47.5°	411.2
50°	326.7
52.5°	247.9
55°	183.8
57.5°	131.3
60°	90.3
62.5°	67.1
65°	49.6
67.5°	38.0
70°	26.2
72.5°	20.4
75°	14.6
77.5°	8.7
80°	5.9
82.5°	3.0
85°	3.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)