

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243801

Luminaire Tested: **LSR8B30D010 EC8B30827 8LBW0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243801  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B30D010 EC8B30827 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 2700 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3062.0 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243801

CATALOG NUMBER: LSR8B30D010 EC8B30827 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P243801

CATALOG NUMBER: LSR8B30D010 EC8B30827 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	54327
5°	55934
10°	60595
15°	66300
20°	68975
25°	68722
30°	64462
35°	54053
40°	37633
45°	21556
50°	11576
55°	4774
60°	1190
65°	306
70°	153
75°	95
80°	142
85°	0



TEST NUMBER: P243801

CATALOG NUMBER: LSR8B30D010 EC8B30827 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.7	5.8
10°-20°	585.3	19.1
20°-30°	921.0	30.1
30°-40°	876.1	28.6
40°-50°	403.9	13.2
50°-60°	91.8	3.0
60°-70°	6.0	0.2
70°-80°	1.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1683.0	55.0
0°-40°	2559.0	83.6
0°-60°	3054.6	99.8
0°-90°	3062.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3062.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1762	
5°	1807	177
15°	2077	585
25°	2020	921
35°	1436	876
45°	494	404
55°	89	92
65°	4	6
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243801

CATALOG NUMBER: LSR8B30D010 EC8B30827 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1761.8
1°	1760.9
2°	1764.3
3°	1774.3
4°	1789.4
5°	1807.0
6°	1828.8
7°	1852.3
8°	1876.6
9°	1905.0
10°	1935.2
11°	1965.4
12°	1997.2
13°	2027.3
14°	2055.0
15°	2076.8
16°	2092.7
17°	2103.6
18°	2108.6
19°	2107.8
20°	2101.9
21°	2091.9
22°	2079.3
23°	2062.5
24°	2043.3
25°	2019.8
26°	1992.2
27°	1957.0
28°	1915.1
29°	1866.5
30°	1810.4
32.5°	1642.0
35°	1435.9
37.5°	1196.3
40°	934.9
42.5°	691.1
45°	494.3
47.5°	350.2
50°	241.3
52.5°	154.1
55°	88.8
57.5°	44.4
60°	19.3
62.5°	7.5
65°	4.2



TEST NUMBER: P243801

CATALOG NUMBER: LSR8B30D010 EC8B30827 8LBW0LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	2.5
70°	1.7
72.5°	1.7
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)