

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844214

Luminaire Tested: **LD6C25DE010B2750 EU6C25B30 6LBWH**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P844214  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C25DE010B2750 EU6C25B30 6LBWH  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2219.0 lumens  
Efficiency: N/A  
Efficacy: 74.5 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 29.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844214

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B30 6LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P844214

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B30 6LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	75027
5°	75000
10°	74425
15°	73922
20°	72795
25°	71133
30°	66979
35°	60619
40°	50609
45°	38787
50°	27462
55°	17318
60°	9769
65°	6343
70°	4135
75°	3050
80°	1831
85°	1824



TEST NUMBER: P844214

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B30 6LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.3	5.8
10°-20°	366.8	16.5
20°-30°	537.8	24.2
30°-40°	559.7	25.2
40°-50°	387.2	17.5
50°-60°	168.6	7.6
60°-70°	51.7	2.3
70°-80°	15.5	0.7
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1033.8	46.6
0°-40°	1593.5	71.8
0°-60°	2149.4	96.9
0°-90°	2219.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2219.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1369	
5°	1363	129
15°	1302	367
25°	1176	538
35°	906	560
45°	500	387
55°	181	169
65°	49	52
75°	14	16
85°	3	2
90°	0	



TEST NUMBER: P844214

CATALOG NUMBER: LD6C25DE010B2750 EU6C25B30 6LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1368.6
2.5°	1371.4
5°	1362.9
7.5°	1351.3
10°	1337.0
12.5°	1322.6
15°	1302.5
17.5°	1276.6
20°	1247.8
22.5°	1216.2
25°	1176.0
27.5°	1124.2
30°	1058.1
32.5°	989.0
35°	905.8
37.5°	813.7
40°	707.2
42.5°	600.9
45°	500.3
47.5°	405.4
50°	322.0
52.5°	244.4
55°	181.2
57.5°	129.5
60°	89.1
62.5°	66.1
65°	48.9
67.5°	37.4
70°	25.8
72.5°	20.2
75°	14.4
77.5°	8.6
80°	5.8
82.5°	2.9
85°	2.9
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)