

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244743

Luminaire Tested: **LSR8B30D010 EC8B30830 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244743
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30830 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2614.0 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244743

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244743

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86		91	88	85		89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80		86	82	79		84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75		81	77	74		80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66		73	69	66		72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62		70	65	62		69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59		66	62	59		65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56		63	59	55		62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	117388
5°	115753
10°	105913
15°	90933
20°	76571
25°	63251
30°	47453
35°	28282
40°	13473
45°	5870
50°	2648
55°	1161
60°	691
65°	379
70°	388
75°	0
80°	142
85°	637



TEST NUMBER: P244743

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.3	13.2
10°-20°	793.7	30.4
20°-30°	842.1	32.2
30°-40°	480.5	18.4
40°-50°	119.1	4.6
50°-60°	23.4	0.9
60°-70°	7.0	0.3
70°-80°	1.5	0.1
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1981.1	75.8
0°-40°	2461.6	94.2
0°-60°	2604.1	99.6
0°-90°	2614.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2614.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3807	
5°	3740	345
15°	2848	794
25°	1859	842
35°	751	480
45°	135	119
55°	22	23
65°	5	7
75°	0	2
85°	2	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P244743

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3806.8
2.5°	3805.1
5°	3739.5
7.5°	3595.4
10°	3382.5
12.5°	3125.3
15°	2848.4
17.5°	2584.5
20°	2333.4
22.5°	2092.0
25°	1859.0
27.5°	1608.8
30°	1332.7
32.5°	1036.0
35°	751.3
37.5°	517.6
40°	334.7
42.5°	212.2
45°	134.6
47.5°	88.0
50°	55.2
52.5°	33.6
55°	21.6
57.5°	17.3
60°	11.2
62.5°	10.3
65°	5.2
67.5°	5.2
70°	4.3
72.5°	2.5
75°	0.0
77.5°	0.8
80°	0.8
82.5°	1.8
85°	1.8
87.5°	0.8
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P244743

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)